

FANYUAN INSTRUMENT (HF) CO., LTD. DOWELL SCIENCE AND TECHNOLOGY (HK) CO., LTD.

ADD: Tianyuan Road 9#, High-tech Zone, Hefei City, China Postal Code: 230088


TEL: +86-551-65232508 FAX: +86-551-65232507 Email: sales@hkdowell.com

Website: http://www.fyichina.com.cn

KX101 Pressley Fiber Bundle Strength Tester











FANYUAN INSTRUMENT (HF) CO., LTD. DOWELL SCIENCE AND TECHNOLOGY (HK) CO., LTD.

ADD: Tianyuan Road 9#, High-tech Zone, Hefei City, China Postal Code: 230088

TEL: +86-551-65232508 FAX: +86-551-65232507 Email: sales@hkdowell.com

Website: http://www.fyichina.com.cn

MODEL NO.

KX101

Application:

Pressley Fiber Bundle Strength Tester is an equipment based on the principle of moment balance measuring force, and use a ramp-type device where a hammer slides freely to measure bundle cotton breaking strength by the distance that the hammer slides.

Related Standards:

STANDARDS GB/T 13783 ISO 3060	
-------------------------------	--

Note: this tester can conform to but not limit to all the standards above, for more standards conformance, please contact us.

Features:

- Special designed Pressley holder with following features:
 - Materials of holder is high hardness steel material;
 - Clamp face seal well and avoid damage specimen or slipping during test;
 - High quality with large quantity of customers including UsterTM.
- Special designed table clamp with following features;
 - ♣ Ensure clamp specimen force of Pressley holder about 70N easy;
 - Let test process much more faster that without table clamp;
 - We are the earliest producer of this table clamp in the world.
- Read out breaking force of bundle cotton fiber immediately after finishing test;



• Level device to decrease experimental error;



With high test accuracy and with good correlation to yarn.



FANYUAN INSTRUMENT (HF) CO., LTD. DOWELL SCIENCE AND TECHNOLOGY (HK) CO., LTD.

ADD: Tianyuan Road 9#, High-tech Zone, Hefei City, China Postal Code: 230088

TEL: +86-551-65232508 FAX: +86-551-65232507 Email: sales@hkdowell.com

Website: http://www.fyichina.com.cn

Key Specification:

Sample thickness of Pressley holderThickness of separator3.2mm

• Range of breaking strength 5~20lbf (25N~90N)

• Coefficient of strength ratio 0.9~1.1

• dimension 380×200×160mm

• weight 4kg

Standard configuration:

No.	Item	Quantity
1	Main machine	1 set
2	Pressley holder	1 pair
3	Fiber processor(table vise)	1 pcs
4	Tweezers	1 pcs
5	Piker	1 pcs
6	Knife	1 pcs
7	Steel comb (crude tooth)	1 pcs
8	Steel comb (fine tooth)	1 pcs

Optional Accessories:

No.	Item	Quantity
1	Torsion balance (JN-B-5)	
2	PL/PH ISO calibration standard cotton	